

# LIFAir LM99 High performance protective mask

SKU: MP30704



Categories: [Health Innovations](#), [Home Health and Home use innovations](#), [Masks](#)

## Short Description:

The unique design of one-way exhaling valve reduces dramatically exhaling resistance Improved comfortability

## Description

[vc\_row][vc\_column][vc\_empty\_space][vc\_column\_text]

### LIFAir LM99 High performance protective mask


New age of mask technology - Be Protected

[/vc\_column\_text][/vc\_column][/vc\_row][vc\_row][vc\_column][vc\_single\_image image="30503" img\_size="full" alignment="center" css\_animation="fadeIn"][/vc\_column][/vc\_row][vc\_row full\_width="stretch\_row\_content\_no\_spaces"][vc\_column][vc\_single\_image image="30506" img\_size="690 x 120" alignment="center" css\_animation="fadeIn"][/vc\_column][/vc\_row][vc\_row full\_width="stretch\_row\_content\_no\_spaces"][vc\_column][vc\_separator border\_width="2" css=".vc\_custom\_1585056633884{margin-top: 20px !important;}"][/vc\_column][/vc\_row][vc\_row][vc\_column][vc\_column\_text]


### LIFAir LM99 Classification

Reaches easily the GB A-level protection GB/T 32610-2016?Daily protective mask technical specifications?


[/vc\_column\_text][/vc\_column][/vc\_row][vc\_row content\_placement="middle" css=".vc\_custom\_1585296645451{padding-top: 24px !important;padding-right: 24px !important;padding-bottom: 24px !important;padding-left: 24px !important;}"][vc\_column][vc\_single\_image image="30507" img\_size="full" alignment="center"

css\_animation="fadeIn" css=".vc\_custom\_1585302195015{margin-top: 25px !important;}"/> Protection level Class A

 Filtration efficiency Filtration efficiency 98 % according to standard test


full\_width="stretch\_row\_content\_no\_spaces"/> EZ Breathing • **Easier Exhaling**

The unique design of one-way exhaling valve reduces dramatically exhaling resistance Improved comfortability


css\_animation="fadeIn"/> National standard

 LIFAair


Inhale resistance ? 75Pa (standard requirements ? 175Pa) Exhale resistance ? 25Pa (standard requirements ? 145Pa) Both inhale and exhale resistance are significantly above the requirements

full\_width="stretch\_row\_content\_no\_spaces"/> ComFitable • **Professional**


**Designed following facial bone anatomy** Fits to Your face comfortably

 Convenient Sealing

Soft cloth fits comfortable and prevents leakages Everyday comfort with smooth finishing

 Nasal supporting structure

Fits firmly with adjustable tip Can be used with glasses without fogging


 contact@medpick.in

(+91) 97900-72534

2086, 9th Cross RPC Layout, Vijayanagar,  
Bangalore - 560040


css\_animation="fadeIn"/>

### Quadruple filtration, with efficiency greater than 98%

img\_size="large" alignment="center"


css\_animation="fadeIn"/>

### How to wear

img\_size="large" alignment="center"

css\_animation="fadeIn"/>

### Recommended time for wearing masks in extreme conditions

img\_size="large" alignment="center"

css\_animation="fadeIn"/>

contact@medpick.in

(+91) 97900-72534

2086, 9th Cross RPC Layout, Vijayanagar,  
Bangalore - 560040